KEYLESS360

THE PERFECT RETROFIT LOCK







SIMPLY PERFECT. PERFECTLY SIMPLE.

Sleek and modern alphanumeric combination locks for shared or assigned use in any wet or dry environment. With a standard vertical 3-hole routing, the Keyless360 is the Perfect Retrofit Lock.

With no batteries to change, no plastic parts and no wires, our locks are maintenance-free resulting in zero operating expenses and two LEED V4 credits.

Standard, premium and custom finishes as well as ADA versions all backed by personal service and the best 5-year comprehensive warranty.







OUR CLIENTS















EQUINOX



































KEYLESS360

ARCHITECTURAL SPECIFICATIONS



PART NUMBER:
KEYLESS360-SN
KEYLESS360-SN-ADA

STANDARD FINISH: SATIN NICKEL



PART NUMBER:
KEYLESS360-MB
KEYLESS360-MB-ADA

PREMIUM FINISH: MATTE BLACK MUNSELL N2/



PART NUMBER:
KEYLESS360-MW
KEYLESS360-MW-ADA

PREMIUM FINISH: MATTE WHITE MUNSELL N9/


10% color discrepancy, and custom pricing options apply.

- 2-digit alphanumeric combination
- Compatible with wood, glass, plastic, phenolic & metal locker doors
- One Master Key has 3 functions: bypasses the code, resets the lock, and retrieves the code - all conveniently from the front.
- Lock features reprogrammable-cylinder. When Master Key is lost or stolen, new Master Key is issued. Simply insert new Master Key and cylinder is reprogrammed - patented solution
- Anti-pick and tamper resistant
- Self-correcting, Breakaway Knob protects against forced entry patented solution
- IP69K Complete dust and water resistance


- Strong 100% metal for long-term and heavy-use no plastic components.
- Large, clear combination digits, double the size of any competitors (5mm tall), that don't fade
- Sufficient digit and dial spacing that prevents accidental lockouts
- Strongest latch (bolt) in the industry and cannot be forced unlocked
- Dead bolt or spring bolt latch type (standard offset: 31mm - addtl available)
- Simple 2 screw installation
- · Surface mounted
- · Accommodates doors 1-21mm thickness

- Easily retrofits from most locks on most locker doors. "The Ultimate Retrofit Lock"
- Ergonomic non-slip grip
- One step twist-&-pull operation
- Knob rotates 90 degrees (from 12 o'clock to 3 o'clock) on left and right hand locks
- · Latch is simply interchangeable to left or right
- Clear locked and unlocked status indicator is visible from a distance
- When disinfecting, mist with liquid that is at least 70% alcohol solution in order to maintain product integrity
- Immediate live response during business hours
- no run around. (sos@keyless.co or 972.331.2770)


TOP VIEW 1-6MM DOOR THICKNESS




TOP VIEW 6-21MM DOOR THICKNESS



FRONT VIEW



DOOR ROUTING



2010 & 2012 ADA STANDARDS FOR ACCESSIBLE DESIGN REQUIREMENTS



- 5% of lockers and their operable parts, the locks, must meet ADA specifications.
- Locks shall be operable with one hand.
- Shall not require tight grasping, pinching, or twisting of the wrist to operate.
- · Shall have a force required to activate of 5lbs (22.2N) maximum.
- \bullet Locks shall be installed maximum 48.00"/1220mm from the floor surface.



Manufactured By:

KEYLESS360

INSTRUCTIONS

USER INSTRUCTIONS

TO LOCK

- 1. Close the door.
- 2. Make sure knob is pointing up to ∆, then set any 2-digit code.
- 3. Turn knob to \triangle .
- 4. Scramble the dials.

CLICK LINK:

https://www.keyless.co/keyless360/instructions/user/

TO UNLOCK

- 1. Re-enter your code.
- 2. Turn the knob up to \triangle .
- 3. Open the door.
- Keeping the knob facing ☐, scramble the dials for the next user.

SCAN QR CODE TO VIEW USER INSTRUCTION VIDEO:



MANAGER INSTRUCTIONS

MASTER KEY CODE BYPASS

(immediate manager access without code obstruction)

- 1. Insert the Master Key pointing towards the \triangle .
- 2. Turn the knob to â and access the locker, then close the door while keeping the knob facing â.
- 3. Return the knob to the △ position, and remove the key.
- *Locker will remain locked and code will remain the same.

USER CODE RETRIEVAL & RESET

(retrieve forgotten user code and reset code for new user)

- 1. Insert the Master Key pointing towards the \triangle and turn the knob to \triangle .
- 2. With each dial: spin until it stops.
 - After setting each dial, the last used code will display.

CLICK LINK:

https://www.keyless.co/keyless360/instructions/reset/

- 3. Turn the knob back to \triangle and remove the key.

SCAN QR CODE TO VIEW
CODE RETRIEVAL & RESET
INSTRUCTION VIDEO:



